



A	Skin	Size	
	38.5" x 38.5"	W	H
		H	
Diamond		Diamond Shown as it will appear on the xpressions unit	

B	Skin	Size	
	28.5" x 28.5"	W	H
		H	
1x1 Single Twist		1x1 Single Twist Shown as it will appear on the Xpressions unit	

C	Skin	Size	
	28" x 28"	W	H
		H	
1x1 Flat Back		1x1 Flat Back Shown as it will appear on the xpressions unit	

D	Skin	Size	
	29" x 29"	W	H
		H	
1x1 Double Twist		1x1 Double Twist Shown as it will appear on the Xpressions unit	

E	Skin	Size	
	28" x 28"	W	H
		H	
1x1 Flat Back		1x1 Flat Back Shown as it will appear on the xpressions unit	

F	Skin	Size	
	28" x 28"	W	H
		H	
1x1 Flat Back		1x1 Flat Back Shown as it will appear on the xpressions unit	

G	Skin	Size	
	29" x 29"	W	H
		H	
1x1 Double Twist		1x1 Double Twist Shown as it will appear on the Xpressions unit	

H	Skin	Size	
	30" x 28"	W	H
		H	
1x1 Horizontal Thread		1x1 Horizontal Thread Shown as it will appear on the Xpressions unit	

I	Skin	Size	
	28" x 28"	W	H
		H	
1x1 Flat Back		1x1 Flat Back Shown as it will appear on the xpressions unit	

J	Skin	Size	
	29" x 29"	W	H
		H	
1x1 Double Twist		1x1 Double Twist Shown as it will appear on the Xpressions unit	

It is recommended that all text and borders be 2" from the finish size

Focus Area Key
 focus area is always 3"-5" inside edge of all four sides on all skin styles and sizes
 see xpressions-snap.com for details