



A	Skin	Size
	W X H	40.5" (1028.7mm)
		40.5" (1028.7mm)
Diamond		Diamond Shown as it will appear on the Xpressions unit

B	Skin	Size
	W X H	29" (736.6mm)
		29" (736.6mm)
1x1 Flat Front		1x1 Flat Front Shown as it will appear on the Xpressions unit

C	Skin	Size
	W X H	29" (736.6mm)
		29" (736.6mm)
1x1 Flat Front		1x1 Flat Front Shown as it will appear on the Xpressions unit

D	Skin	Size
	W X H	29" (736.6mm)
		29" (736.6mm)
1x1 Flat Front		1x1 Flat Front Shown as it will appear on the Xpressions unit

E	Skin	Size
	W X H	29" (736.6mm)
		29" (736.6mm)
1x1 Flat Front		1x1 Flat Front Shown as it will appear on the Xpressions unit

F	Skin	Size
	W X H	29" (736.6mm)
		29" (736.6mm)
1x1 Flat Back		1x1 Flat Front Shown as it will appear on the Xpressions unit

G	Skin	Size
	W X H	29" (736.6mm)
		29" (736.6mm)
1x1 Flat Back		1x1 Flat Front Shown as it will appear on the Xpressions unit

H	Skin	Size
	W X H	29" (736.6mm)
		29" (736.6mm)
1x1 Flat Back		1x1 Flat Front Shown as it will appear on the Xpressions unit

I	Skin	Size
	W X H	29" (736.6mm)
		29" (736.6mm)
1x1 Flat Back		1x1 Flat Front Shown as it will appear on the Xpressions unit

J	Skin	Size
	W X H	40.5" (1028.7mm)
		40.5" (1028.7mm)
Diamond		Diamond Shown as it will appear on the Xpressions unit

It is recommended that all text and borders be 2" from the finish size

**Focus Area Key**  
 focus area is always 3"-5" inside edge of all four sides on all skin styles and sizes