



A	Skin	Size
	W X H	59" (1498.6mm)
		59" (1498.6mm)
2x2 Flat Shown as it will appear on the Xpressions unit		

B	Skin	Size	C	Skin	Size
	W X H	29.5" (749.3mm)		W X H	29" (736.6mm)
		29.5" (749.3mm)			31" (787.4mm)
1x1 Single Twist Shown as it will appear on the Xpressions unit			1x1 Vertical Thread Shown as it will appear on the Xpressions unit		

D	Skin	Size	E	Skin	Size
	W X H	29" (736.6mm)		W X H	29.5" (749.3mm)
		31" (787.4mm)			29.5" (749.3mm)
1x1 Vertical Thread Shown as it will appear on the Xpressions unit			1x1 Single Twist Shown as it will appear on the Xpressions unit		

F	Skin	Size	G	Skin	Size
	W X H	31" (787.4mm)		W X H	31" (787.4mm)
		29" (736.6mm)			29" (736.6mm)
1x1 Horizontal Thread Shown as it will appear on the Xpressions unit			1x1 Horizontal Thread Shown as it will appear on the Xpressions unit		

H	Skin	Size
	W X H	29" (736.6mm)
		29" (736.6mm)
1x1 Flat Front Shown as it will appear on the Xpressions unit		

I	Skin	Size
	W X H	31" (787.4mm)
		29" (736.6mm)
1x1 Horizontal Thread Shown as it will appear on the Xpressions unit		

J	Skin	Size
	W X H	31" (787.4mm)
		29" (736.6mm)
1x1 Horizontal Thread Shown as it will appear on the Xpressions unit		

K	Skin	Size
	W X H	29" (736.6mm)
		29" (736.6mm)
1x1 Flat Front Shown as it will appear on the Xpressions unit		

L	Skin	Size
	W X H	29" (736.6mm)
		29" (736.6mm)
1x1 Flat Front Shown as it will appear on the Xpressions unit		

M	Skin	Size
	W X H	29.5" (749.3mm)
		29.5" (749.3mm)
1x1 Single Twist Shown as it will appear on the Xpressions unit		

N	Skin	Size
	W X H	29" (736.6mm)
		31" (787.4mm)
1x1 Vertical Thread Shown as it will appear on the Xpressions unit		

O	Skin	Size
	W X H	29" (736.6mm)
		31" (787.4mm)
1x1 Vertical Thread Shown as it will appear on the Xpressions unit		

P	Skin	Size
	W X H	29.5" (749.3mm)
		29.5" (749.3mm)
1x1 Single Twist Shown as it will appear on the Xpressions unit		

Q	Skin	Size
	W X H	29" (736.6mm)
		29" (736.6mm)
1x1 Flat Front Shown as it will appear on the Xpressions unit		

It is recommended that all text and borders be 2" from the finish size

**Focus Area Key**  
 focus area is always 3"-5" inside edge of all four sides on all skin styles and sizes