



| A | Skin | Size |
|----------|---|---|
| | 59" (1498.6mm) X 59" (1498.6mm) | W |
| | | H |
| 2x2 Flat | | 2x2 Flat Shown as it will appear on the Xpressions unit |

| B | Skin | Size | C | Skin | Size |
|------------------|---|---|------------------|---|---|
| | 29.5" (749.3mm) X 29.5" (749.3mm) | W | | 29.5" (749.3mm) X 29.5" (749.3mm) | W |
| | | H | | | H |
| 1x1 Single Twist | | 1x1 Single Twist Shown as it will appear on the Xpressions unit | 1x1 Single Twist | | 1x1 Single Twist Shown as it will appear on the Xpressions unit |

| D | Skin | Size | E | Skin | Size |
|------------------|---|---|------------------|---|---|
| | 29.5" (749.3mm) X 29.5" (749.3mm) | W | | 29.5" (749.3mm) X 29.5" (749.3mm) | W |
| | | H | | | H |
| 1x1 Single Twist | | 1x1 Single Twist Shown as it will appear on the Xpressions unit | 1x1 Single Twist | | 1x1 Single Twist Shown as it will appear on the Xpressions unit |

| F | Skin | Size | G | Skin | Size |
|------------------|---|---|------------------|---|---|
| | 29.5" (749.3mm) X 29.5" (749.3mm) | W | | 29.5" (749.3mm) X 29.5" (749.3mm) | W |
| | | H | | | H |
| 1x1 Single Twist | | 1x1 Single Twist Shown as it will appear on the Xpressions unit | 1x1 Single Twist | | 1x1 Single Twist Shown as it will appear on the Xpressions unit |

| J | Skin | Size | K | Skin | Size |
|------------------|---|---|-------------------|--|--|
| | 29.5" (749.3mm) X 29.5" (749.3mm) | W | | 29" (736.6mm) X 62" (1574.8mm) | W |
| | | H | | | H |
| 1x1 Single Twist | | 1x1 Single Twist Shown as it will appear on the Xpressions unit | 1x2 Double Thread | | 1x2 Double Thread Shown as it will appear on the Xpressions unit |

| H | Skin | Size |
|-------------------|--|--|
| | 29" (736.6mm) X 62" (1574.8mm) | W |
| | | H |
| 1x2 Double Thread | | 1x2 Double Thread Shown as it will appear on the Xpressions unit |

| I | Skin | Size |
|------------------|---|---|
| | 29.5" (749.3mm) X 29.5" (749.3mm) | W |
| | | H |
| 1x1 Single Twist | | 1x1 Single Twist Shown as it will appear on the Xpressions unit |

| L | Skin | Size |
|------------------|---|---|
| | 29.5" (749.3mm) X 29.5" (749.3mm) | W |
| | | H |
| 1x1 Single Twist | | 1x1 Single Twist Shown as it will appear on the Xpressions unit |

| M | Skin | Size |
|-----------------------|---|--|
| | 31" (787.4mm) X 29" (736.6mm) | W |
| | | H |
| 1x1 Horizontal Thread | | 1x1 Horizontal Thread Shown as it will appear on the Xpressions unit |

| N | Skin | Size |
|-----------------------|---|--|
| | 31" (787.4mm) X 29" (736.6mm) | W |
| | | H |
| 1x1 Horizontal Thread | | 1x1 Horizontal Thread Shown as it will appear on the Xpressions unit |

| O | Skin | Size |
|------------------|---|---|
| | 29.5" (749.3mm) X 29.5" (749.3mm) | W |
| | | H |
| 1x1 Single Twist | | 1x1 Single Twist Shown as it will appear on the Xpressions unit |

It is recommended that all text and borders be 2" from the finish size

Focus Area Key
focus area is always 3"-5" inside edge of all four sides on all skin styles and sizes